



For more Information
please call

1-800-Belden1



General Description:

Security & Alarm Cable, Plenum-CMP 4-22 AWG stranded bare copper conductors with Flammarrest® insulation, Flammarrest® jacket with ripcord

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
4	22	7	BC - Bare Copper

Total Number of Conductors: 4

Insulation

Insulation Material:

Insulation Trade Name	Insulation Material	Wall Thickness (mm)
Flammarrest®	LS PVC - Low Smoke Polyvinyl Chloride	0.203

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Trade Name	Outer Jacket Material	Nom. Wall Thickness (mm)
Flammarrest®	LS PVC - Low Smoke Polyvinyl Chloride	0.381

Outer Jacket Ripcord: Yes

Overall Cable

Overall Cabling Lay Length & Direction:

Length (mm)	Twists (twist/m)
76.1997	13.124

Overall Cabling Color Code Chart:

Color
Black
Red
White
Green

Overall Nominal Diameter: 3.531 mm

Mechanical Characteristics (Overall)

Operating Temperature Range: 0°C To +75°C

Bulk Cable Weight: 22.323 Kg/Km

Max. Recommended Pulling Tension: 161.914 N

Min. Bend Radius/Minor Axis: 35.560 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMP
CEC/C(UL) Specification:	CMP
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	NFPA 262
C(UL) Flame Test:	FT6

Plenum/Non-Plenum

Plenum (Y/N):	Yes
Non-Plenum Number:	5502UE

Electrical Characteristics (Overall)

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)
88.587

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
52.8241

Max. Operating Voltage - UL:

Voltage
300 V RMS

Max. Recommended Current:

Current
2.2 Amps per conductor @ 25°C

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
6502UE 004Z1000	1,000 FT	18.000 LB	YELLOW		4 #22 FLRST FLRST
6502UE 877C500	500 FT	7.500 LB	NATURAL		4 #22 FLRST FLRST
6502UE 877U1000	1,000 FT	16.000 LB	NATURAL		4 #22 FLRST FLRST
6502UE 877U500	500 FT	8.500 LB	NATURAL		4 #22 FLRST FLRST
6502UE 877Z1000	1,000 FT	18.000 LB	NATURAL		4 #22 FLRST FLRST
6502UE 8771000	1,000 FT	16.000 LB	NATURAL	C	4 #22 FLRST FLRST
6502UE 877500	500 FT	8.000 LB	NATURAL		4 #22 FLRST FLRST

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 2 Revision Date: 03-13-2013

© 2019 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).