

## 7111WS Multi-Conductor - 600V C-TC+ Control Cables for Extreme Flexing



For more Information  
please call

1-800-Belden1



### General Description:

18 AWG stranded (114x38) bare copper conductors, PVC-Nylon insulation, Braid Shield, Oil- and Abrasion-resistant PVC Jacket.

### Physical Characteristics (Overall)

#### Conductor

##### AWG:

# Conductors	AWG	Stranding	Conductor Material
3	18	114x38	BC - Bare Copper

Total Number of Conductors: 4

#### Ground Wire

Ground Wire (Y/N): Y

Ground Wire AWG: 18

Ground Wire Stranding: 114x38

Ground Wire Conductor Material: BC - Bare Copper

Ground Wire Insulation Material: PVC/Nylon - Polyvinyl Chloride/Nylon

#### Insulation

##### Insulation Material:

Insulation Material	Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.406
Nylon	0.127

##### Insulation Color Code Chart:

Color	Description
Red	Individually Numbered

#### Inner Jacket

##### Inner Jacket Material:

Inner Jacket Material	Nom Wall (mm)
TPE - Thermoplastic Elastomer	0.635

#### Outer Shield

##### Outer Shield Material:

Type	Outer Shield Material	Coverage (%)	Dia. (mm)
Braid	Tinned Copper	85.000	7.544

#### Outer Jacket

##### Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
TPE - Thermoplastic Elastomer	1.194

#### Overall Cable

Overall Nominal Diameter: 9.931 mm

### Mechanical Characteristics (Overall)

Operating Temperature Range: -50°C To +90°C

Other Temperature Range: Flexing: -5°C To +90°C

## 7111WS Multi-Conductor - 600V C-TC+ Control Cables for Extreme Flexing

<b>UL Temperature Rating:</b>	90°C (UL AWM Style 2587)
<b>Bulk Cable Weight:</b>	142.867 Kg/Km
<b>Max. Recommended Pulling Tension:</b>	409.234 N
<b>Min. Bend Radius (Continuous Flexing):</b>	99.060 mm
<b>Flex Cycle Rating:</b>	10 Million Flexes

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

<b>NEC/(UL) Specification:</b>	TC-ER, WTTTC
<b>CEC/C(UL) Specification:</b>	600V Type CIC TC
<b>AWM Specification:</b>	UL Style 2587 (600 V 90°C), UL Style 21486 (1000 V 90°C)
<b>CSA Specification:</b>	AWM I/II A/B
<b>EU Directive 2011/65/EU (ROHS II):</b>	Yes
<b>EU Directive 2000/53/EC (ELV):</b>	Yes
<b>EU Directive 2002/95/EC (RoHS):</b>	Yes
<b>EU RoHS Compliance Date (mm/dd/yyyy):</b>	10/01/2005
<b>EU Directive 2002/96/EC (WEEE):</b>	Yes
<b>EU Directive 2003/11/EC (BFR):</b>	Yes
<b>EU REACH SVHC Present:</b>	Yes
<b>CA Prop 65 (CJ for Wire &amp; Cable):</b>	Yes
<b>MII Order #39 (China RoHS):</b>	Yes

#### Flame Test

<b>UL Flame Test:</b>	UL1685 FT4/IEEE 1202 Vertical Tray Flame Test
<b>CSA Flame Test:</b>	FT4
<b>IEEE Flame Test:</b>	1202

#### Suitability

<b>Suitability - Burial:</b>	Yes
<b>Sunlight Resistance:</b>	Yes
<b>Oil Resistance:</b>	Yes - Oil Res II
<b>Non-halogenated:</b>	No

#### Plenum/Non-Plenum

<b>Plenum (Y/N):</b>	No
----------------------	----

### Electrical Characteristics (Overall)

#### Nom. Conductor DC Resistance:

<b>DCR @ 20°C (Ohm/km)</b>
18.702

### Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
7111WS 0031000	1,000 FT	101.000 LB	ORANGE	C	3 #18 + GRD PVC/NYL TPE BRDTPE
7111WS 0035000	5,000 FT	545.000 LB	ORANGE		3 #18 + GRD PVC/NYL TPE BRDTPE

#### Notes:

C = CRATE REEL PUT-UP.

## 7111WS Multi-Conductor - 600V C-TC+ Control Cables for Extreme Flexing

Revision Number: 4    Revision Date: 10-02-2013

© 2019 Belden, Inc.  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.