

METRIC MEASUREMENT VERSION

76125WS Multi-Conductor - 300V Foil/Spiral Shield, Continuous Flexing Data Applications Up to 6 Million Flex Life Cycles



For more Information
please call

1-800-Belden1

General Description:

26 AWG stranded (7x33) tinned copper conductors, PVC insulation, Aluminum/Polyester Foil Shield, Tinned copper spiral shield, 90% coverage, oil-resistant PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
25	26	7x34	TC - Tinned Copper

Insulation

Insulation Material:

Insulation Material	Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.254

Insulation Color Code Chart:

Number	Color
1	Black
2	Red
3	White
4	Green
5	Orange
6	Blue
7	Brown
8	Yellow
9	Violet
10	Slate
11	Pink
12	Tan
13	Red/Green
14	Red/Yellow
15	Red/Black
16	White/Black
17	White/Red
18	White/Green
19	White/Yellow
20	White/Blue
21	White/Brown
22	White/Orange
23	White/Slate
24	White/Violet
25	White/Black/Red

Outer Shield

Outer Shield Material:

Layer #	Type	Outer Shield Material	Coverage (%)
1	Tape	Aluminum/Mylar	100.000
2	Serve	TC - Tinned Copper	90.000

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	1.016

Overall Cable

Overall Nominal Diameter: 9.017 mm

Mechanical Characteristics (Overall)

Bulk Cable Weight:	122.032 Kg/Km
Max. Recommended Pulling Tension:	280.237 N
Min. Bend Radius/Minor Axis:	71.120 mm
Min. Bend/Installation:	71.120 mm
Min. Bend Radius (Continuous Flexing):	71.120 mm
Flex Cycle Rating:	6 Million Flexes

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CM
CEC/C(UL) Specification:	CMG
EU Directive 2011/65/EU (ROHS II):	Yes
MII Order #39 (China RoHS):	Yes
Customer Part Number Reference Specification:	AWM/STYLE 10002, AWM/STYLE 2661, CSA AWM I/II A/B, EU Directive 2011/65/EU(RoHS2), REACH Regulation (EC 1907/2006), California Proposition 65

Flame Test

CSA Flame Test:	FT4
------------------------	-----

Suitability

Suitability - Burial:	Yes
------------------------------	-----

Electrical Characteristics (Overall)

Nom. Inductance:

Inductance (µH/m)
0.656

Nom. Capacitance Conductor to Conductor:

Freq. (MHz)	Capacitance (pF/m)
0.001	91.868

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
137.802

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)
9.187

Max. Operating Voltage - UL:

Voltage
300V

Notes (Overall)

Notes: Temperature Range -10 to 105°C(static), +5 to 105°C (dynamic)

Put Ups and Colors:

No put ups and colors are available for this product

Revision Number: 0 Revision Date: 09-27-2017

© 2020 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not

METRIC MEASUREMENT VERSION

76125WS Multi-Conductor - 300V Foil/Spiral Shield, Continuous Flexing Data Applications Up to 6 Million Flex Life Cycles

ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.