


7838A Multi-Conductor - T1/DS1 Central Office Interconnect/Cross Connect Cable

For more Information
please call

1-800-Belden1



General Description:

22 AWG solid tinned copper conductors, twisted pairs, Datalene® insulation, individually shielded with 100% Beldfoil® shield, 24 AWG solid tinned copper drain wire each pair, PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material	Dia. (mm)
2	22	Solid	TC - Tinned Copper	0.64516

Total Number of Conductors: 4

Insulation

Insulation Material:

Insulation Trade Name	Insulation Material
Datalene®	PO w/Foam PO - Polyolefin w/Foam Polyolefin

Inner Shield

Inner Shield Material:

Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

Inner Shield Drain Wire AWG:

AWG
24

Inner Shield Drain Wire Stranding: Solid

Inner Shield Drain Wire Conductor Material: TC - Tinned Copper

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cable

Overall Nominal Diameter: 5.131 x 9.144 mm

Pair

Pair Color Code Chart:

Number	Color
1	Blue & White/Blue
2	Orange & White/Orange

Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +75°C

Bulk Cable Weight: 49.111 Kg/Km

Max. Recommended Pulling Tension: 137.894 N

Min. Bend Radius/Minor Axis: 50.800 mm

7838A Multi-Conductor - T1/DS1 Central Office Interconnect/Cross Connect Cable

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CM
CEC/C(UL) Specification:	CM
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	UL1685 UL Loading
----------------	-------------------

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Description	Impedance (Ohm)
@ 1 MHz	100.000

Nom. Inductance:

Inductance (µH/m)
0.78744

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)
47.5745

Nominal Velocity of Propagation:

VP (%)
72

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
54.7927

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100m)
0.772	1.411

Max. Operating Voltage - UL:

Voltage
300 V RMS

Max. Recommended Current:

Current
3.5 Amps per conductor @ 25°C

Differential Impedance @ 1 MHz:	105
---------------------------------	-----

Notes (Overall)

Notes: Single conductors are dual insulated. The outer layer of insulation must be stripped off before attaching modular connectors. Use a stripping tool such as Cooper Tools Xcelite model 103-S, or equivalent with a mechanical stop to avoid nicking the inner insulation. RJ-45 Compatible.

7838A Multi-Conductor - T1/DS1 Central Office Interconnect/Cross Connect Cable

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
7838A 0601000	1,000 FT	37.000 LB	CHROME	C	2 FS PR #22 PP/FPE PVC PARA
7838A 0602000	2,000 FT	74.000 LB	CHROME	C	2 FS PR #22 PP/FPE PVC PARA
7838A 0605000	5,000 FT	180.000 LB	CHROME	C	2 FS PR #22 PP/FPE PVC PARA

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 02-23-2017

© 2019 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.