

8412 Multi-Conductor - Two-Conductor, Low-Impedance Cable



For more Information
please call

1-800-Belden1



General Description:

20 AWG stranded (7x28) high-conductivity TC conductors, EPDM insulation, TC braid shield (85% coverage), EPDM jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material	Dia. (mm)
2	20	26x34	High Conductivity TC - Tinned Copper	0.9398

Total Number of Conductors: 2

Insulation

Insulation Material:

Insulation Material	Wall Thickness (mm)
EPDM - Ethylene Propylene Diene Monomer Rubber	0.584

Outer Shield

Outer Shield Material:

Layer #	Type	Outer Shield Material	Coverage (%)
1	Braid	Cotton	
2	Braid	TC - Tinned Copper	85

Outer Shield Separator Material: Cotton Wrap

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
EPDM - Ethylene Propylene Diene Monomer Rubber

Overall Cable

Overall Cabling Color Code Chart:

Number	Color
1	White
2	Black

Overall Cabling Separator Material: Rayon Braid

Overall Nominal Diameter: 6.655 mm

Mechanical Characteristics (Overall)

Operating Temperature Range: -50°C To +90°C

Non-UL Temperature Rating: 90°C

Bulk Cable Weight: 65.481 Kg/Km

Max. Recommended Pulling Tension: 444.820 N

Min. Bend Radius/Minor Axis: 69.850 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

EU Directive 2011/65/EU (ROHS II): Yes

METRIC MEASUREMENT VERSION

8412 Multi-Conductor - Two-Conductor, Low-Impedance Cable

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 01/01/2004

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

Plenum/Non-Plenum

Plenum (Y/N): No

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)

67.000

Nom. Inductance:

Inductance (µH/m)

0.59058

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)

108.273

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/m)

190.298

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)

34.779

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)

14.765

Max. Operating Voltage - Non-UL:

Voltage

600 V RMS

Max. Recommended Current:

Current

4 Amps per conductor @ 25°C

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8412 0021000	1,000 FT	47.000 LB	RED	C	2 #20 EPDM BRD EPDM
8412 0041000	1,000 FT	47.000 LB	YELLOW	C	2 #20 EPDM BRD EPDM
8412 0061000	1,000 FT	47.000 LB	BLUE, LIGHT	C	2 #20 EPDM BRD EPDM
8412 010U1000	1,000 FT	46.000 LB	BLACK		2 #20 EPDM SHLD EPDM
8412 010U500	500 FT	23.500 LB	BLACK		2 #20 EPDM SHLD EPDM
8412 010100	100 FT	5.200 LB	BLACK		2 #20 EPDM BRD EPDM
8412 0101000	1,000 FT	47.000 LB	BLACK	C	2 #20 EPDM BRD EPDM
8412 010250	250 FT	12.000 LB	BLACK		2 #20 EPDM BRD EPDM
8412 010500	500 FT	24.000 LB	BLACK	C	2 #20 EPDM BRD EPDM

Notes:

C = CRATE REEL PUT-UP.

8412 Multi-Conductor - Two-Conductor, Low-Impedance Cable

Revision Number: 1 Revision Date: 09-11-2017

© 2019 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).