



For more Information
please call

1-800-Belden1



General Description:

22 AWG solid conductors, PVC insulation, tinned copper, twisted pairs, individually shielded w/Beldfoil® (100% coverage), 22 AWG solid TC drain wire, overall PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
3	22	Solid	TC - Tinned Copper

Total Number of Conductors: 6

Insulation

Insulation Material:

Insulation Material	Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.3302

Inner Shield

Inner Shield Material:

Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)
Beldfoil® (Z-Fold®)	Tape	Aluminum Foil-Polyester Tape	100

Inner Shield Drain Wire AWG:

AWG
22

Inner Shield Drain Wire Stranding: Solid

Inner Shield Drain Wire Conductor Material: TC - Tinned Copper

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.9398

Overall Cable

Overall Nominal Diameter: 7.087 mm

Pair

Pair Color Code Chart:

Number	Color
1	Black & Red
2	Black & White
3	Black & Green

Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +80°C

UL Temperature Rating: 80°C (UL AWM Style 2464)

Bulk Cable Weight: 62.504 Kg/Km

Max. Recommended Pulling Tension: 386.993 N

Min. Bend Radius/Minor Axis: 76.200 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMG, MPG
CEC/C(UL) Specification:	CMG, MPG
AWM Specification:	UL Style 2464 (300 V 80°C)
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	UL1685 FT4 Loading
CSA Flame Test:	FT4

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Inductance:

Inductance (µH/m)	0.62339
-------------------	---------

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)	131.24
--------------------	--------

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/m)	252.637
--------------------	---------

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)	54.7927
---------------------	---------

Ind. Pair Nominal Shield DC Resistance @ 20 Deg. C: 39.372 Ohm/km

Max. Operating Voltage - UL:

Voltage	300 V RMS
---------	-----------

Max. Recommended Current:

Current	2 Amps per conductor @ 25°C
---------	-----------------------------

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8767 060U500	500 FT	22.500 LB	CHROME		3 PR FS #22 PVC PVC
8767 0601000	1,000 FT	46.000 LB	CHROME	C	3 PR FS #22 PVC PVC
8767 060500	500 FT	23.000 LB	CHROME		3 PR FS #22 PVC PVC

Notes:

METRIC MEASUREMENT VERSION

8767 Multi-Conductor - Audio, Control and Instrumentation Cable

C = CRATE REEL PUT-UP.

Revision Number: 2 Revision Date: 10-05-2012

© 2019 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).