

8814 Multi-Conductor - Class 1 Speaker Cable



For more Information
please call

1-800-Belden1



General Description:

14 AWG, stranded (19x26H) bare copper conductors, PVC/Nylon insulation, PVC jacket.

Usage (Overall)

Suitable Applications: AUDITORIUM , STADIUM , RACE TRACK , CHURCH , TEMPLE ,
SYNAGOGUE , PLACE OF ASSEMBLY , CASINO , SOUND

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
2	14	19x26H	BC - Bare Copper

Total Number of Conductors: 2

Insulation

Insulation Material:

Layer #	Insulation Material
1	PVC
2	Nylon

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC

Overall Cable

Overall Nominal Diameter: 8.331 mm

Pair

Pair Color Code Chart:

Number	Color
1	Black & White

Mechanical Characteristics (Overall)

Wet Temperature Range: -30°C To +75°C

Dry Temperature Range: -30°C To +90°C Dry

Bulk Cable Weight: 81.851 Kg/Km

Max. Recommended Pulling Tension: 422.579 N

Min. Bend Radius/Minor Axis: 88.900 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: NPLF, TC, THHN/THWN Singles

EU Directive 2011/65/EU (ROHS II): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 03/15/12

METRIC MEASUREMENT VERSION

8814 Multi-Conductor - Class 1 Speaker Cable

EU Directive 2002/96/EC (WEEE): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

Flame Test

UL Flame Test: UL1581 Vertical Tray

CSA Flame Test: FT4

IEEE Flame Test: 1202

Suitability

Suitability - Indoor: Yes

Suitability - Outdoor: Yes

Suitability - Burial: Yes

Sunlight Resistance: Yes

Plenum/Non-Plenum

Plenum (Y/N): No

Electrical Characteristics (Overall)

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)

8.531

Max. Operating Voltage - UL:

Voltage

600

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8814 0101000	1,000 FT	59.000 LB	BLACK	C	2 #14 PVC/NYL PVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 0 Revision Date: 05-19-2014

© 2019 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.