

For more Information
please call

1-800-Belden1



General Description:

22 AWG solid bare copper-covered steel conductor, polyethylene insulation, bare copper braid shield (85% coverage), PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (mm)
1	22	Solid	BCCS - Bare Copper Covered Steel	0.635

Total Number of Conductors: 1

Insulation

Insulation Material:

Insulation Material	Dia. (mm)
PE - Polyethylene	3.7084

Outer Shield

Outer Shield Material:

Type	Outer Shield Material	Coverage (%)
Braid	BC - Bare Copper	85

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cable

Overall Nominal Diameter: 6.147 mm

Mechanical Characteristics (Overall)

Operating Temperature Range: -40°C To +80°C

Non-UL Temperature Rating: 80°C

Bulk Cable Weight: 49.111 Kg/Km

Max. Recommended Pulling Tension: 298.029 N

Min. Bend Radius/Minor Axis: 63.500 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CMX

CEC/C(UL) Specification: CMX

AWM Specification: UL Style 1354 (30 V 80°C)

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
RG Type:	59/U

Flame Test

UL Flame Test:	VW-1
----------------	------

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)

75

Nom. Inductance:

Inductance (µH/m)

0.367472

Nom. Capacitance Conductor to Shield:

Capacitance (pF/m)

63.6514

Nominal Velocity of Propagation:

VP (%)

66

Nominal Delay:

Delay (ns/m)

5.05274

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)

164.05

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)

14.7645

Nom. Attenuation:

Freq. (MHz) Attenuation (dB/100m)

1	1.9686
10	3.6091
50	7.8744
100	11.1554
200	16.0769
400	22.967
700	31.8257
900	36.4191
1000	39.372

Nom. Power Rating:

Freq. (MHz) Rating (W)

50	470
100	310

300	160
500	115
1000	76

Max. Operating Voltage - UL:

Voltage
150 V RMS

Max. Operating Voltage - Non-UL:

Voltage
1700 V RMS

Minimum Return Loss:

Description	Freq. (MHz)	Start Freq. (MHz)	Stop Freq. (MHz)	Min. RL (dB)
		5	450	23

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9244 010U1000	1,000 FT	35.000 LB	BLACK		RG-59/U TYPE COAX
9244 010U500	500 FT	18.000 LB	BLACK		RG-59/U TYPE COAX
9244 0101000	1,000 FT	36.000 LB	BLACK		RG-59/U TYPE COAX

Revision Number: 3 Revision Date: 05-14-2007

© 2019 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).