

## 9414 Multi-Conductor - Audio, Control and Instrumentation Cable



For more Information  
please call

1-800-Belden1



### General Description:

22 AWG stranded (7x30) tinned copper conductors, semi-rigid PVC insulation, twisted pair, overall Beldfoil® shield (100% coverage), 22 AWG stranded TC drain wire, jacket-striated PVC.

### Physical Characteristics (Overall)

#### Conductor

##### AWG:

# Pairs	AWG	Stranding	Conductor Material
1	22	7x30	TC - Tinned Copper

Total Number of Conductors: 2

#### Insulation

##### Insulation Material:

Insulation Material	Wall Thickness (mm)
S-R PVC - Semi-Rigid Polyvinyl Chloride	0.279

#### Outer Shield

##### Outer Shield Material:

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

##### Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
22	7x30	TC - Tinned Copper

#### Outer Jacket

##### Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.889

#### Overall Cable

Overall Nominal Diameter: 4.572 mm

#### Pair

##### Pair Color Code Chart:

Number	Color
1	Black & White

### Mechanical Characteristics (Overall)

Operating Temperature Range:	-20°C To +80°C
UL Temperature Rating:	80°C (UL AWM Style 2464)
Bulk Cable Weight:	31.252 Kg/Km
Max. Recommended Pulling Tension:	120.101 N
Min. Bend Radius/Minor Axis:	50.800 mm

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

NEC/(UL) Specification: CMG

METRIC MEASUREMENT VERSION

## 9414 Multi-Conductor - Audio, Control and Instrumentation Cable

CEC/C(UL) Specification:	CMG
AWM Specification:	UL Style 2464 (300 V 80°C)
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	10/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

### Flame Test

CSA Flame Test:	FT4
-----------------	-----

### Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

## Electrical Characteristics (Overall)

### Nom. Characteristic Impedance:

Impedance (Ohm)

38

### Nom. Inductance:

Inductance (µH/m)

0.59058

### Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)

164.05

### Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/m)

311.695

### Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)

52.496

### Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)

41.0125

### Max. Operating Voltage - UL:

Voltage

300 V RMS

### Max. Recommended Current:

Current

2.9 Amps per conductor @ 25°C

## Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9414 T35U1000	1,000 FT	23.000 LB	BEIGE, PALE FAWN		2 #22 PVC SHLD FRPVC
9414 T351000	1,000 FT	23.000 LB	BEIGE, PALE FAWN	C	2 #22 PVC SHLD FRPVC
9414 T35500	500 FT	11.500 LB	BEIGE, PALE FAWN		2 #22 PVC SHLD FRPVC
9414 T355000	5,000 FT	115.000 LB	BEIGE, PALE FAWN		2 #22 PVC SHLD FRPVC

### Notes:

C = CRATE REEL PUT-UP.

## 9414 Multi-Conductor - Audio, Control and Instrumentation Cable

Revision Number: 2    Revision Date: 11-12-2012

© 2019 Belden, Inc.  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).