

9729ZH Multi-Conductor - GreenChoice Shielded Twisted Pair Cable



For more Information
please call

1-800-Belden1



General Description:

24 AWG stranded (7x32) tinned copper conductors, Datalene® insulation, twisted pairs, individually Beldfoil® shielded (100% coverage), 24 AWG stranded tinned copper drain wire, NHRPO jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material	Dia. (mm)
2	24	7x32	TC - Tinned Copper	0.6096

Total Number of Conductors: 4

Insulation

Insulation Material:

Insulation Trade Name	Insulation Material	Wall Thickness (mm)	Dia. (mm)
Datalene®	FPE - Foam Polyethylene	0.470	1.549

Inner Shield

Inner Shield Material:

Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)
Beldfoil® (Z-Fold®)	Tape	Aluminum Foil-Polyester Tape	100

Inner Shield Drain Wire AWG:

AWG
24

Inner Shield Drain Wire Stranding: 7x32

Inner Shield Drain Wire Conductor Material: TC - Tinned Copper

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
NHRPO

Overall Cable

Overall Nominal Diameter: 6.756 mm

Pair

Pair Color Code Chart:

Number	Color
1	Black & Red
2	Black & White

Pair Lay Length & Direction:

Lay Length (mm)	Twists (twist/m)
27.94	35.763

Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +80°C

UL Temperature Rating: 80°C

Bulk Cable Weight: 53.575 Kg/Km

9729ZH Multi-Conductor - GreenChoice Shielded Twisted Pair Cable

Max. Recommended Pulling Tension:	97.860 N
Min. Bend Radius/Minor Axis:	82.550 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMG
CEC/C(UL) Specification:	CMG
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	05/08/2012
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Other Specification:	UL AWM 21088

Flame Test

UL Flame Test:	UL1685 FT4 Loading
C(UL) Flame Test:	FT4

Suitability

Suitability - Indoor:	Yes
Non-halogenated:	Yes

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)

100

Nom. Inductance:

Inductance (µH/m)

0.75463

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)

41.0125

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/m)

76.1192

Nominal Velocity of Propagation:

VP (%)

76

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)

78.744

Ind. Pair Nominal Shield DC Resistance @ 20 Deg. C: 49.215 Ohm/km

Nom. Attenuation:

9729ZH Multi-Conductor - GreenChoice Shielded Twisted Pair Cable

Freq. (MHz)	Attenuation (dB/100m)
.384	2.42794
.7056	2.85447
.768	2.88728
1.024	3.08414
1.4112	3.31381
1.536	3.37943
2.048	3.70753
2.8224	4.23249
3.072	4.42935
4.096	5.15117
5.6448	5.84018
6.144	6.03704
8.192	6.98853
11.2896	8.03845
12.288	8.43217
24.576	11.7132

Max. Operating Voltage - UL:

Voltage
300 V RMS (UL AWM Style 2493)

Max. Recommended Current:

Current
1 Amp per conductor @ 25°C

Notes (Overall)

Notes: Datalene® insulation features include low dielectric constant and a dissipation factor for high-speed, low-distortion data handling. Physical properties include good crush resistance and light weight.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9729ZH 0601000	1,000 FT	37.000 LB	CHROME		2 FS PR #24 FHDPE FHDPE
9729ZH 0605000	500 FT	20.000 LB	CHROME		2 FS PR #24 FHDPE FHDPE

Revision Number: 0 Revision Date: 08-16-2016

© 2019 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).