


IBDN25P Multi-Conductor - Category 5e Nonbonded-Pair Cable

For more Information
please call

1-800-Belden1



General Description:

CAT5e (100MHz), 25-Pair, U/UTP-Unshielded, Plenum-CMP, Premise Backbone Cable, 24 AWG solid bare copper conductors, FEP insulation, Ripcord, FEP jacket

Usage (Overall)

Suitable Applications:

Premise Backbone Cable, Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM, NTSC/PAL Component or Composite Video, AES/EBU Digital Audio, AES51, RS-422, Noisy Environments

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
25	24	Solid	BC - Bare Copper

Total Number of Conductors:

50

Insulation

Insulation Material:

Insulation Material
FEP - Fluorinated Ethylene Propylene

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
FEP - Fluorinated Ethylene Propylene

Outer Jacket Diameter:

Nom. Dia. (mm)
10.922

Outer Jacket Ripcord:

Yes

Pair

Pair Color Code Chart:

Number	Color
1	White & Blue
2	White & Orange
3	White & Green
4	White & Brown
5	White & Gray
6	Red & Blue
7	Red & Orange
8	Red & Green
9	Red & Brown
10	Red & Gray
11	Black & Blue

IBDN25P Multi-Conductor - Category 5e Nonbonded-Pair Cable

12	Black & Orange
13	Black & Green
14	Black & Brown
15	Black & Gray
16	Yellow & Blue
17	Yellow & Orange
18	Yellow & Green
19	Yellow & Brown
20	Yellow & Gray
21	Purple & Blue
22	Purple & Orange
23	Purple & Green
24	Purple & Brown
25	Purple & Gray

Mechanical Characteristics (Overall)

Storage Temperature Range:	-40°C To +75°C
Installation Temperature Range:	0°C To +60°C
Operating Temperature Range:	-40°C To +60°C
Bulk Cable Weight:	203.883 Kg/Km
Max. Recommended Pulling Tension:	667.230 N
Min. Bend Radius/Minor Axis:	109.220 mm
Min. Bend/Installation:	109.220 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMP
CEC/C(UL) Specification:	CMP
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Telecommunications Standards:	Category 5e - TIA 568.C.2
Other Specification:	NEMA WC-63.1 Category 5e

Flame Test

C(UL) Flame Test:	FT6
CSA Flame Test:	FT6

Plenum/Non-Plenum

Plenum (Y/N):	Yes
Non-Plenum Number:	IBDN25R

Electrical Characteristics (Overall)

Nom. Mutual Capacitance:

Capacitance (pF/m)
45.934

Maximum Capacitance Unbalance (pF/100 m):	330
--	-----

IBDN25P Multi-Conductor - Category 5e Nonbonded-Pair Cable

Nominal Velocity of Propagation:

VP (%)
72.000

Maximum Delay:

Delay (ns/100 m)
538 @ 100MHz

Max. Delay Skew:

Delay Skew (ns/100 m)
45

Maximum Conductor DC Resistance:

DCR @ 20°C (Ohm/100 m)
9.38

Max. Operating Voltage - UL:

Voltage
300 V RMS

Maximum DCR Unbalanced:

DCR Unbalance @ 20°C (%)
5

Electrical Characteristics-Premise (Overall)

Premise Cable Electricals:

Freq. (MHz)	Max. Attenuation (dB/100 m)	Min. PSNEXT (dB)	Min. SRL (dB)	Fitted Imp. (Ohms)
.772	1.800	64		
1	2.000	62.3	20	100 ± 15%
4	4.100	53.3	23.0	100 ± 15%
8	5.800	48.8	24.5	100 ± 15%
10	6.500	47.3	25	100 ± 15%
16	8.200	44.3	25	100 ± 15%
20	9.300	42.8	25	100 ± 15%
25	10.400	41.3	24.3	100 ± 15%
31.25	11.700	39.9	23.6	100 ± 15%
62.5	17.000	35.4	21.5	100 ± 15%
100	22.000	32.3	20.1	100 ± 15%

Notes (Overall)

Notes: Jacket sequentially marked at 2 ft. intervals. Third party verified to TIA/EIA-568-B.2, Category 5e.

Reference (Overall)

Previous Part Number: 24577123

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
IBDN25P 008CUT	1 FT	0.000	GRAY		CAT5E 25PR U/UTP CMP CUT
IBDN25P 0081000	1,000 FT	151.000 LB	GRAY		CAT5E 25PR U/UTP CMP REEL

Revision Number: 4 Revision Date: 03-25-2014

© 2020 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

IBDN25P Multi-Conductor - Category 5e Nonbonded-Pair Cable

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.